



Sealing curve of HS-LACQUER VIKTOR 84 on PRIMER VIKTOR 200 (Al)



The values specified are only approximate. Under different conditions and with diverse types of the heat-seal plastic films, the real values might differ significantly from the specified ones.

Version May 2020

Sealing curve of HS-LACQUER VIKTOR 84 on PRIMER VIKTOR 200 (Al)




HS-LACQUER VIKTOR
84
7 g/m² on
PRIMER VIKTOR 200
2 g/m²
Al: 30 µm
Width of sample: 15 mm

The values specified are only approximate. Under different conditions and with diverse types of the heat-seal plastic films, the real values might differ significantly from the specified ones.

Version May 2020

Sealing curve of HS-LACQUER VIKTOR 84 on PRIMER VIKTOR 880 (Al)



The values specified are only approximate. Under different conditions and with diverse types of the heat-seal plastic films, the real values might differ significantly from the specified ones.
 Version May 2020